



## Clip light, Type: W1R-WORK



### Order data

Order number	081226 W1R-WORK
GTIN	4058205032094
Item class	04B

### Description

#### Version:

Ultra-compact, powerful, versatile: the Ledlenser W1R Work is a handy clip light for tradespeople, security personnel and DIY fans. It can easily be attached at any time by clip or magnet, e.g. to work clothing, caps or metal surfaces. The superior Ledlenser light quality provides precise illumination in two different brightness levels. Thanks to the 360° swivel joint and swivelling lamp head, the small companion light delivers light exactly where it is needed. The integrated battery can be recharged quickly and easily via USB-C. Other clever features include a nubbed surface for a strong grip, a handy transport lock and a low-battery warning function.

- **Ultra-compact, rechargeable clip light with two brightness levels.**
- **360° swivel joint and swivelling lamp head for precise and flexible illumination.**
- **Flexible mounting via robust clip or magnet.**
- **Integrated Li-ion battery; easily rechargeable via USB-C, with battery and charge level indicator.**
- **Transport lock prevents light from being inadvertently turned on.**

#### Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

### Technical description

Battery voltage	3.7 V
Illumination time	1.5 - 7 h

## Data sheet

IP Index of Protection	IP 54
Overall width	38 mm
Manufacturer's designation	W1R Work
Power supply	Mains operated
Illumination	60 - 220 lm
Bulb	LED module
Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
ATEX zone	None
Overall length	32 mm
Overall height	76 mm
Colour temperature	6000 - 7500 K
Weight	392 g
CRI value	70
Battery capacity	0.74 Ah
Type of product	Work lamp