

Storage rack for lifting tackle with theft prevention, Type: M



Order data

Order number	918621 M
GTIN	2050002073616
Item class	97B

Description

Version:

Steel tube stand for storage of lifting tackle such as chains, ropes, lifting slings etc.. With 2 height adjustable cross beams and 12 galvanised and adjustable double suspension hooks. Easy disassembly and reassembly for mobile use on building sites. Supplied disassembled, easy assembly with instructions.

Including theft prevention, consisting of 4 retaining bars including welded-on chain. Retaining bars are pushed through the suspension hooks. Padlock can be used with max. frame dia. 7 mm. With 4 castors, 2 with parking brake.

Colour:

RAL 7035 light grey **powder-coated**.

Note:

Additional adjustable galvanized double hooks can be found under No. 918623 size 6 at www.hoffmann-group.com.

Suitable padlock can be found in Volume 2 Hand tools under No. 085812 and No. 085814.

Technical description

Number of hooks	12
Weight	100 kg

Height	1934 mm
Depth	900 mm
Load capacity per hook	75 kg
Configurator relevant	no
maximum load capacity	1000 kg
Width	1890 mm
Type of product	Lifting tackle trolley

Accessories

Double hook 6 pieces Type 6	918623 6
Theft prevention Type 4	918622 4