

bimos

ESD swivel chair, synthetic leather, with glides and footrest ring, high, Type: ESD**Order data**

Order number	972673 ESD
GTIN	4016849944005
Item class	96B

Description**Version:**

Seat and backrest made of conductive ESD imitation leather covering. Comfortable and breathable, hard-wearing. Comfortable cushion with ergonomic backrest and horizontal stitching, with practical push handles. With ergonomic package: synchronous technology incl. weight adjustment. Continuous conductive connection from the foam to the ESD castors/glides. Backrest with conductive plastic shell and push handles.

Weight adjustment from 45 – 120 kg.

Standard:

Leitfähig nach DIN 61340-5-1.

Technical description

Height adjustment version	Gas pressure spring
Series	Work-Tec Ergo
Seat angle adjustment in degrees	6°
Backrest height	580 mm

Seat depth adjustment range	60 mm
Colour of seat material	black
Seat depth	470 mm
Seat width	460 mm
Seat tilt adjustment	yes
Backrest height adjustment range	60 mm
Load capacity chair	120 kg
electrostatic characteristic	EGB/ESD
Height adjustment range	590 - 860 mm
Type of product	ESD work chair

Accessories

ESD castors(1 set = 5 pieces)	963189
-------------------------------	--------