

Garant
Face driver set With morse taper / cylindrical, clockwise operation, Type: 4

Order data

Order number	327455 4
GTIN	4067263557999
Item class	31G

Description
Version:

- **Constant face driver head with 60° tip angle for use in turning and grinding.**
- **Face driver with spring-loaded, clampable centring point for a backlash-free, stable clamping situation.**
- **High concentricity thanks to fully ground mechanical components.**
- **Perfect in combination with our lathe centres No. 321720, 311750 or 321770.**
- **Conveniently in the GARANT system box 630320.**

Supplied with:

- **1 pc. face driver base body No. 327465 (suitable for clockwise and anti-clockwise rotation).**
- **2 pcs. centring point No. 327488.**
- **2 pcs. driver heads No. 327470.**

Technical description

Working range Ø	17 - 32 mm
Working range Ø	26 - 50 mm
Centre tip Ø	10; 16 mm
Type of product	Face driver

Accessories

Centring point for face driver Centring tip Ø D 16 mm	327488 16
Face driverWith morse taper / cylindrical Type 4	327465 4
Direct toothed driver head, groundRight-hand Working range Ø 17-32 mm	327470 17-32
Direct toothed driver head, groundRight-hand Working range Ø 26-50 mm	327470 26-50
Centring point for face driver Centring tip Ø D 10 mm	327488 10