

Garant
Face driver With morse taper / cylindrical, Type: D32

Order data

Order number	327465 D32
GTIN	4067263558156
Item class	31G

Description
Version:

Face driver with spring-loaded centring point. The clamping of the centring point when the driver head makes flat surface contact ensures a backlash-free, stable clamping situation. High concentricity thanks to fully ground mechanical components, without centring point and driver heads, suitable for clockwise and anti-clockwise operation. Fully mechanical design with spring force. No leakages from hydraulic fluid. Option for direct clamping on the head on raised collar in soft shaped jaws.

Suitable for:

Lathe centres No. 321720, 321750 and 321770.

Optional extras:

Driver heads No. 327470 - 327486 and old version No. 327601 – 327651, centring point No. 327488, taper sleeves No. 327492.

Technical description

maximum body Ø	75 mm
Weight	2.3 kg
Version	cylindrical
Shank Ø D _s	55 mm
Length C	148 mm

Type of product

Face driver