

Garant
Face driver With morse taper / cylindrical, Type: 4

Order data

| | |
|--------------|---------------|
| Order number | 327465 4 |
| GTIN | 4067263558132 |
| Item class | 31G |

Description
Version:

Face driver with spring-loaded centring point. The clamping of the centring point when the driver head makes flat surface contact ensures a backlash-free, stable clamping situation. High concentricity thanks to fully ground mechanical components, without centring point and driver heads, suitable for clockwise and anti-clockwise operation. Fully mechanical design with spring force. No leakages from hydraulic fluid. Option for direct clamping on the head on raised collar in soft shaped jaws.

Suitable for:

Lathe centres No. 321720, 321750 and 321770.

Optional extras:

Driver heads No. 327470 - 327486 and old version No. 327601 – 327651, centring point No. 327488, taper sleeves No. 327492.

Technical description

| | |
|------------------------|-------------|
| maximum body Ø | 75 mm |
| Weight | 2.7 kg |
| Version | Morse taper |
| Shank Ø D _s | 67 mm |
| Length C | 170 mm |

Type of product

Face driver