



Cordless nibbler, Type: 71321161



Order data

Order number	078108 71321161
GTIN	4014586898568
Item class	03F

Description

Version:

- **Very economical operating costs due to long working life of die and matrix.**
- **QuickIN quick-change system for quick die and matrix changing without tools**
- **Working direction can be changed without tools.**

Cordless sheet metal nibbler for portable use.

- **Slim design ensures optimum handling even under difficult working conditions.**
- **Highly suitable for trapezoidal sheet up to 1.3 mm thick and up to 85 mm step depth.**

Flexible nibblers with high manoeuvrability for thin sheet metal, trapezoidal sheet, corrugated sheet and sections.

Supplied with:

Including L-BOXX, **without** battery and **without** charger.

Note:

Suitable batteries can be found under No. 073851 – No. 073858 or starter set under No. 073863 – No. 073867. Chargers are listed under No. 073866.

Technical description

Packaging	Modular case (L-Boxx)
-----------	-----------------------

suitable battery - supplier / battery type / voltage	Bosch 18 V
Battery voltage	18 V
Radius of the smallest curve	30 mm
Type of rechargeable battery	Lithium-ion
Cutting speed	1.9 m/min
maximum vibration to EN	<2.5 m/s ²
maximum material thickness steel 800 N/mm ²	0.7 mm
Power supply	Rechargeable battery-powered
maximum material thickness steel 400 N/mm ²	1.6 mm
Cutting width	5 mm
Number of rechargeable batteries contained	0
Manufacturer's designation	ABLK 18 1.6 E AS
Weight	2.1 kg
Type of product	Nibblers