



Cordless pipe cutter, Type: M12PCSS/0



Order data

Order number	078218 M12PCSS/0
GTIN	4058546370350
Item class	03L

Description

Version:

Compact cordless pipe cutter with stainless cutting head. **Automatic adaptation** to the pipe \varnothing . **Quick cutting**, e.g. cuts 15 mm \varnothing copper pipe in less than 3 seconds. Overall width 40 mm, minimum wall clearance 40 mm. Supplied **without batteries and charger**. Pipe cutter for **stainless steel pipes**, \varnothing 12 – 28 mm.

Note:

Batteries can be found from No. 073814.

Technical description

Speed range	0 - 500 min ⁻¹
maximum vibration to EN	<2,5 m/s ²
Number of rechargeable batteries contained	0
Manufacturer's designation	M12 PCSS-0
maximum pipe \varnothing copper	12 - 28 mm
Weight	1.5 kg
Type of rechargeable battery	Lithium-ion
Power supply	Mains operated
Battery voltage	12 V

maximum pipe Ø stainless steel	12 - 28 mm
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Type of product	Pipe cutters