

LESSMANN®
THE GERMAN BRUSH COMPANY**Wheel brush with shank knotted stainless steel wire 0.50 mm, Type: 75X10****Order data**

Order number	574405 75X10
GTIN	4017359010839
Item class	57L

Description**Version:**Knotted steel wire, **shank Ø 6 mm.****Application:**

Very aggressive brushing effect with high wear resistance. For removal of rust, scale and burrs.

Technical description

Length of brush section H ₁	15 mm
Bristle width L ₁	12 mm
Number of twisted knots	18
Shank Ø D _s	6 mm
Brush Ø D ₁	75 mm
Bristle thickness	0.5 mm
maximum speed	25000 min ⁻¹
Brush material	Stainless steel wire
Twisted knotting	left-hand plait
Type of product	Wheel brush