



Mobile workbench with universal tool set 137 pieces, Type: 1



Order data

Order number	689100 1
GTIN	4018754344383
Item class	66H

Description

Version:

Mobile workbench WB 621 with 7 drawers. The 2 upper drawers are equipped with a **137-piece Stahlwille tool set**, consisting of the following configuration: Spanners, pliers, 1/4-inch and 1/2-inch sockets, striking tools, circlip pliers, screwdrivers and supplementary articles. The contents of the other 5 drawers can be individually selected.

The cabinet section has a height-adjustable storage shelf. The cabinet section and workbench are locked with a common key. 4 keys are supplied.

The general-purpose tool selection fits precisely in two-tone PE rigid foam inlays, in which each tool has its own defined place in the workbench. The drawers in the roller cabinet are unlocked using a central locking mechanism with a cylinder lock on the side and a removable key. The workbench has a large work surface with birch marine ply worktop, FSC certified, 1150×500×30 mm. Can be wired using two rubberised feed-throughs and removable cable duct on the rear. With paper roll holder and side hole grid for hooks, e.g. for larger tools. The oil-resistant and acid-resistant wheels (Ø 125 mm) have fibre shields to protect the bearings against dirt and fibres/threads, with two parking brakes.

Supplied with:

Workbench: 1 pc. WB 621

Spanner set, 22 pieces: 1 pc. each combination spanner No. 613500 size 6; 7; 8; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22; 24

5 pcs. ratchet ring spanner size 8, 10; 13; 17; 19 mm

1 pc. single open ended spanner, max. width across flats 34 mm
 Pliers set, 4 pieces: 1 pc. water pump pliers size 240 mm
 1 pc. heavy-duty side cutter size 160 mm
 1 pc. snipe nose pliers size 200 mm
 1 pc. combination pliers size 180 mm
 Socket set, 72 pieces: 1/4 inch + 1/2 inch socket set, 52 pieces
 1 pc. bit set with 1 pc. screwdriver holder, 21 pieces
 Striking tool set, 7 pieces: 1 pc. engineer's hammer size 500 g
 1 pc. soft-faced hammer size 35 mm
 1 pc. flat chisel size 175 mm
 2 pcs. pin punch size 150×6 mm; 3.4 mm
 1 pc. drift punch size 120×4 mm
 1 pc. centre punch size 100×10 mm
 Circlip pliers set, 4 pieces: 4 pcs. size A21; A2; J2; J21
 Screwdriver set + supplementary articles, 28 pieces: 3 pcs. screwdriver for slot-head size 2.5; 4; 10 mm
 3 pcs. screwdriver for Phillips size PH1; PH2; PH3
 1 pc. L-wrench set for internal Torx®, 8 pcs.
 1 pc. hexagon key L-wrench set, 9 pcs.
 1 pc. cable knife
 1 pc. tape measure size 3 m
 1 pc. wooden folding rule size 2 m
 1 pc. mini magnetic retriever
 1 pc. rod lamp

Note:**Tools are supplied loose.****Technical description**

Width	1150 mm
Height	1045 mm
Depth	500 mm
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Square drive	1/2 in
Square drive	1/4 in
Cylinder lock	modular barrel
Type of product	Roller cabinet

Accessories

Combination spanner Width across flats 6 mm	613500 6
Combination spanner Width across flats 24 mm	613500 24
Combination spanner Width across flats 16 mm	613500 16
Combination spanner Width across flats 14 mm	613500 14
Combination spanner Width across flats 22 mm	613500 22
Combination spanner Width across flats 17 mm	613500 17
Combination spanner Width across flats 7 mm	613500 7
Combination spanner Width across flats 15 mm	613500 15
Combination spanner Width across flats 21 mm	613500 21
Combination spanner Width across flats 12 mm	613500 12
Combination spanner Width across flats 10 mm	613500 10
Combination spanner Width across flats 8 mm	613500 8
Combination spanner Width across flats 18 mm	613500 18
Combination spanner Width across flats 13 mm	613500 13
Combination spanner Width across flats 19 mm	613500 19
Combination spanner Width across flats 11 mm	613500 11