

**Garant**
**Workshop set, Number of tools: 22**

**Order data**

Order number	955072 22
GTIN	4067263169178
Item class	91A

**Description**
**Version:**

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. Upper layer is anthracite, the underlying contrast colour is grey, thus indicates any missing tools.

Rigid foam inlay basic set for one complete drawer – usable area 20×20G.

**Suitable for:**

GridLine Ready-to-go workbenches, GridLine Vario workbenches with 24G casing, GridLine 24G casing, GridLine 24×24G tool cabinets, GridLine 20×20G drawers, GridLine XL ToolCar No. 914590.

**Supplied with:**

Rigid foam inlay, empty No. 952001 size 955072: 1 pc.

GARANT caliper No. 410100 size 150: 1 pc.

GARANT external micrometer No. 420402 size 0–25: 1 pc.

GARANT tape measure No. 462201 size 2.5: 1 pc.

GARANT spirit level No. 467010 size 250: 1 pc.

GARANT double open ended spanner No. 610600 size 8×9; 10×11; 12×13; 14×15; 17×19: 1 pc. each

GARANT hexagon key L-wrench with retention ball No. 627132 size 9: 1 pc.

GARANT screwdriver for slot-head No. 660032 size 2.5; 4; 5.5: 1 pc. each

GARANT screwdriver for Phillips No. 667702 size 1; 2: 1 pc. each

GARANT torch No. 081505 size 125: 1 pc.  
 GARANT combination pliers No. 700940 size 160: 1 pc.  
 GARANT side cutter No. 724840 size 160: 1 pc.  
 GARANT engineer's hammer No. 750110 size 200: 1 pc.  
 GARANT heavy duty scissors No. 769240 size 175: 1 pc.  
 GARANT pliers wrench No. 813501 size 180: 1 pc.  
 GARANT universal knife No. 845020: 1 pc.

## Technical description

Drawer usable area in G	20×20
Depth in G	20
Width in G	20
Version	for roller cabinet drawer
Number of tools	22
Depth	500 mm
Width	500 mm
Rigid foam quality LD45, thickness	30 mm
Square drive	1/4 in
Smallest suitable drawer front height	100 mm
Type of product	Rigid foam inlay

## Accessories

Rigid foam inlay for tool sets suitable for rigid foam set 955072	952001 955072
Vernier caliper Measuring range 150 mm	410100 150
External micrometer Measuring range 0-25 mm	420402 0-25
Tape measure with viewing window Band length 2,5 m	462201 2,5
Spirit level with selectable magnet Length 250 mm	467010 250
Double open ended spanner Jaw widths 10X11 mm	610600 10X11
Double open ended spanner Jaw widths 12X13 mm	610600 12X13

Double open ended spanner Jaw widths 14X15 mm	610600 14X15
Double open ended spanner Jaw widths 17X19 mm	610600 17X19
Double open ended spanner Jaw widths 8X9 mm	610600 8X9
Hexagon key L-wrench set, with retainer ballchrome-plated Number of screwdrivers 9	627132 9
Screwdriver for slot-head, with 2-component Haptoprene handle Blade width b 2,5 mm	660032 2,5
Screwdriver for slot-head, with 2-component Haptoprene handle Blade width b 4 mm	660032 4
Screwdriver for slot-head, with 2-component Haptoprene handle Blade width b 5,5 mm	660032 5,5
Screwdriver for Phillips, with 2-component Haptoprene handle Cross-head size 1	667702 1
Screwdriver for Phillips, with 2-component Haptoprene handle Cross-head size 2	667702 2
LED torcheswith batteries Type 125 mm	081505 125
Combination pliers, chrome-plated, with 2-component grips overall length 160 mm	700940 160
Diagonal side cutter chrome-plated, with grips overall length 160 mm	724840 160
Engineer's hammer withhandle protection collar Weight without handle 200 g	750110 200
General-purpose scissors with titanium coating overall length 175 mm	769240 175
Pliers wrench overall length 180 mm	813501 180
General-purpose knife with 2-component handlewith 3 blades, 18 mm	845020