


Socket set 1/4 inch, Number of tools: 29



Order data

| | |
|--------------|---------------|
| Order number | 955161 29 |
| GTIN | 4067263103066 |
| Item class | 91A |

Description

Version:

Popular tool sets in two-colour PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

Supplied with:

Rigid foam inlay, empty No. 952001 size 955161: 1 pc.

GARANT hexagon socket 1/4 inch No. 631029 size 3.5; 4; 4.5; 5; 5.5; 6; 7; 8; 9; 10; 11; 12; 13; 14: 1 pc. each

HOLEX screwdriver bit for slot-head, 1/4 inch No. 631613 size 3.5; 5.5: 1 pc. each

HOLEX screwdriver bit for Phillips 1/4 inch No. 631623 size 1; 2: 1 pc. each

GARANT hexagon screwdriver bit 1/4 inch long No. 631729 size 2.5; 3; 4; 5; 6: 1 pc. each

GARANT reversible ratchet, 1/4 inch No. 632025 size 1/4: 1 pc.

GARANT extension 1/4 inch No. 632429 size 50; 100: 1 pc. each

GARANT spinner handle 1/4 inch No. 632829 size 146: 1 pc.

GARANT T-handle 1/4 inch No. 633029 size 116: 1 pc.

GARANT universal joint 1/4 inch No. 633529 size 1/4: 1 pc.

Technical description

| | |
|------------------------------------|--------|
| Width | 383 mm |
| Number of tools | 29 |
| Depth | 115 mm |
| Rigid foam quality LD45, thickness | 30 mm |
| Square drive | 1/4 in |

| | |
|--------------------------------|------------------|
| suitable for shadowboard depth | 115 mm |
| Type of product | Rigid foam inlay |

Accessories

| | |
|---|---------------|
| Rigid foam inlay for tool sets suitable for rigid foam set 955161 | 952001 955161 |
| Hexagon socket, 1/4 inch Width across flats 10 mm | 631029 10 |
| Hexagon socket, 1/4 inch Width across flats 11 mm | 631029 11 |
| Hexagon socket, 1/4 inch Width across flats 12 mm | 631029 12 |
| Hexagon socket, 1/4 inch Width across flats 13 mm | 631029 13 |
| Hexagon socket, 1/4 inch Width across flats 14 mm | 631029 14 |
| Hexagon socket, 1/4 inch Width across flats 3,5 mm | 631029 3,5 |
| Hexagon socket, 1/4 inch Width across flats 4 mm | 631029 4 |
| Hexagon socket, 1/4 inch Width across flats 4,5 mm | 631029 4,5 |
| Hexagon socket, 1/4 inch Width across flats 5 mm | 631029 5 |
| Hexagon socket, 1/4 inch Width across flats 5,5 mm | 631029 5,5 |
| Hexagon socket, 1/4 inch Width across flats 6 mm | 631029 6 |
| Hexagon socket, 1/4 inch Width across flats 7 mm | 631029 7 |
| Hexagon socket, 1/4 inch Width across flats 8 mm | 631029 8 |
| Hexagon socket, 1/4 inch Width across flats 9 mm | 631029 9 |
| Bit socket for slot-head, 1/4 inch Blade width 3,5 mm | 631613 3,5 |
| Bit socket for slot-head, 1/4 inch Blade width 5,5 mm | 631613 5,5 |
| Bit socket for Phillips, 1/4 inch Cross-head size 1 | 631623 1 |
| Bit socket for Phillips, 1/4 inch Cross-head size 2 | 631623 2 |
| Hexagon bit socket, 1/4 inchlong Hexagon 2,5 mm | 631729 2,5 |
| Hexagon bit socket, 1/4 inchlong Hexagon 3 mm | 631729 3 |
| Hexagon bit socket, 1/4 inchlong Hexagon 4 mm | 631729 4 |
| Hexagon bit socket, 1/4 inchlong Hexagon 5 mm | 631729 5 |

| | |
|--|------------|
| Hexagon bit socket, 1/4 inch long Hexagon 6 mm | 631729 6 |
| Reversible ratchet, 1/4 inch with ejector Type 1/4 | 632025 1/4 |
| Extension, 1/4 inch overall length 100 mm | 632429 100 |
| Extension, 1/4 inch overall length 50 mm | 632429 50 |
| Spinner handle, 1/4 inch overall length 146 mm | 632829 146 |
| T-handle, 1/4 inch overall length 116 mm | 633029 116 |
| Universal joint 1/4 inch Type 1/4 | 633529 1/4 |