



Knotted end brush Steel wire, Brush \varnothing D1 \times bristle thickness: 19X0,35mm



Order data

| | |
|--------------|----------------|
| Order number | 574850 19X0,35 |
| GTIN | 4067263935070 |
| Item class | 57H |

Description

Version:

Smooth, **knotted** wire, crimped into steel ferrule, **shank \varnothing 6 mm**, even density, extremely wear-resistant.

Application:

For deburring, removing paint, and for all moderate to heavy brushing jobs. **As speed increases the brush opens, this allows it to be introduced even into tight spaces**, e.g. when brushing the inside of casings.

Technical description

| | |
|--|-------------------------|
| Shank \varnothing D _s | 6 mm |
| maximum speed | 20000 min ⁻¹ |
| Brush \varnothing D ₁ | 19 mm |
| Bristle thickness | 0.35 mm |
| Length of brush section H ₁ | 28 mm |
| Number of twisted knots | 6 |
| Brush material | Steel wire |
| Twisted knotting | left knotted |
| Type of product | End brush |

