

HOLEX**Knotted end brush Steel wire, Brush \varnothing D1 \times bristle thickness: 22X0,25mm****Order data**

Order number	574850 22X0,25
GTIN	4067263935087
Item class	57H

Description**Version:**

Smooth, **knotted** wire, crimped into steel ferrule, **shank \varnothing 6 mm**, even density, extremely wear-resistant.

Application:

For deburring, removing paint, and for all moderate to heavy brushing jobs. **As speed increases the brush opens, this allows it to be introduced even into tight spaces**, e.g. when brushing the inside of casings.

Technical description

Bristle thickness	0.25 mm
Length of brush section H ₁	28 mm
Brush \varnothing D ₁	22 mm
Number of twisted knots	6
maximum speed	20000 min ⁻¹
Shank \varnothing D _s	6 mm
Brush material	Steel wire
Twisted knotting	left knotted
Type of product	End brush

