



Knotted end brush Steel wire, Brush $\varnothing D_1 \times$ bristle thickness: 28X0,35mm



Order data

Order number	574850 28X0,35
GTIN	4067263935100
Item class	57H

Description

Version:

Smooth, **knotted** wire, crimped into steel ferrule, **shank \varnothing 6 mm**, even density, extremely wear-resistant.

Application:

For deburring, removing paint, and for all moderate to heavy brushing jobs. **As speed increases the brush opens, this allows it to be introduced even into tight spaces**, e.g. when brushing the inside of casings.

Technical description

Length of brush section H_1	28 mm
maximum speed	20000 min^{-1}
Brush $\varnothing D_1$	28 mm
Number of twisted knots	12
Shank $\varnothing D_s$	6 mm
Bristle thickness	0.35 mm
Brush material	Steel wire
Twisted knotting	left knotted
Type of product	End brush

