

Yale

Hydraulic hand pump HPS, Number of steps / Tank volume: 2/4l



Order data

Order number	086050 2/4
GTIN	4025092159111
Item class	08Y

Description

Version:

All components and attachments satisfy **metric standard ranges**, which considerably simplifies assembly, service, and the procurement of spare parts. **100 % compatibility** with all commercially-available 700 bar hydraulic systems.

2-stage hand pump **with rapid movement setting** (except size 1/0.7). The switch from first to second stage is performed automatically. **With pressure limiting valves adjustable in the range 0 – 700 bar. All-metal construction** with fine-adjustment release valve, bleeding and filling screw and a carrying eye on the operating handle.

Supplied with:

Filled with oil, without manometer.

Note:

Closed systems are pre-mounted ex works, filled and air bled.

For hydraulic hand pump see No. 086050, hydraulic hose No. 086081, pressure gauge No. 086087.

Technical description

Number of pressure stages	2
usable tank volume	4000 ml
Delivery quantity per load stroke (2nd stage)	2 ml
Delivery quantity per no-load stroke (1st stage)	11 ml

Weight	13 kg
Type of product	Hydraulic hand pump

Accessories

Manometer kit GYA-63 Display range 0-1000 bar	086087 0-1000
---	---------------