

Garant
GARANT Softcut® 90° shoulder mill MTC, with bore, Ø D / Zeff: 50/3mm

Order data

Order number	215161 50/3
GTIN	4045197455208
Item class	210

Description
Version:

High precision square shoulder milling cutter with irregular pitch for very smooth cutting, very high precision and cutting power. High performance indexable square shoulder milling cutter **with special geometry for reduced cutting forces for MTC applications** under **unstable conditions** or **for spindles with low drive power**.

Application:

For corner milling to large depths, also slotting. General use in all steels including stainless steels. Especially for **MTC (Multi Task Cutting)** use on the new generation of turning / milling centres (**MTM**).

Note:

Use GARANT torque screwdriver TQ No. **211750 size 3.8** with bit No. **674252 size 15IP**. The insert pocket must be modified when using indexable inserts with a radius greater than 3.1 mm.

Technical description

Cutting edge Ø D _c	50 mm
maximum cutting depth a _{p max}	55 mm
Overall length L _{tot}	72 mm
Mounting bore Ø	22 mm

Pack of insert screws	219808 (15IP; 3.8 Nm)
suitable indexable insert	AP.. 1805..
Number of effective inserts Z_{eff}	3
Series	Softcut®
Number of indexable inserts	12
Shank type	with bore
Setting angle κ	90 degrees
Milling application	Corner milling
Milling application	Ramping
Milling application	Circular milling
Spacing of the cutters	unequal spacing
Through-coolant	yes
Machining strategy	MTC
Tool exchange	PowerCard
Type of product	End / face mill

Accessories

Set of insert screws 10-piece	219808
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
Torque screwdriver, fixed setting set torque 3,8 N·m	211750 3,8