

**Extension cable for F, B, PL, CZ, 250 V, Type: 10N****Order data**

Order number	081183 10N
GTIN	4003644009329
Item class	08B

**Description****Version:**

**Certified for exterior use and for use in humid environments (IP44).**

With sockets for **countries F, B, PL, CZ**. Resistant to oil, petrol, UV radiation.

**Neoprene rubber cable** with splash-proof rubber plug and socket.

**Function:**

IP44: Protected against splashed water from all directions and protected against penetration by foreign bodies with  $\varnothing > 1 \text{ mm}$ , however tools and wires should be kept away.

**Technical description**

Cable class	H07RN-F
Cable structure	3G1.5
Material cable	Neoprene
Cable length	10 m
suitable for countries	F; B; PL; CZ
Type	10N

impact-resistant and splash-proof	Category 2 (K2) to BGI
IP Index of Protection	IP 44
Power supply	Mains operated
Plug type, input	E
Product name attribute	250 V
AC supply voltage	250 V
Type of product	Extension cable

---

## Accessories

CableFix cable suspension system Type S	081191 S
CableFix cable suspension system Type XL	081191 XL
CableFix cable suspension system Type L	081191 L