

Garant
NC spotting drills, 120°, Ø Ds: 20 mm

Order data

Order number	231501 20
GTIN	4045197644305
Item class	21Y

Description
Version:
With Weldon shank.

Spotting drill suitable for insert shape: 120

Number of cutting edges Z: 1

 maximum hole Ø d₁: 17 mm

 maximum drilling depth l₁: 5 mm

Shank length h: 70 mm

 Overall length L_{tot}: 100 mm

Indexable insert size: 16

Technical description

Insert screw	231540_TX15 (2.5 Nm)
maximum hole Ø d ₁	17 mm
Overall length L _{tot}	100 mm
Shank length h	70 mm
Indexable insert size	16

Shank $\varnothing D_s$	20 mm
maximum drilling depth l_1	5 mm
ISO code indexable insert	SOGT 11T3
Number of cutting edges Z	1
Shank	Weldon shank
Spotting drill suitable for insert shape	120
Product name attribute	120°
Through-coolant	no
Point angle	120°
Type of product	Indexable drill

Accessories

PrecisionBit for Torx®, shank E 6.3 Torx® profile TX15	674248 TX15
8 mm blade with magnetwith 1/4 inch bit holder overall length 50 mm	659874 50
Torx® clamping screw Drive TX15	231540 TX15
Torque screwdriverwith scale, to take interchangeable blades maximum torque 500 cNm	659906 500