

Garant
Copy milling head, HB730, Ø D h10: 12mm

Order data

| | |
|--------------|---------------|
| Order number | 210360 12 |
| GTIN | 4045197523433 |
| Item class | 21M |

Technical description

| | |
|---|-------------------------|
| maximum cutting depth $a_{p,max}$ in steel $< 900 \text{ N/mm}^2$ | 3.6 mm |
| Head length l | 16 mm |
| Cutter Ø D | 12 mm |
| Flute length L_2 | 9 mm |
| Feed f_z for copy milling in steel $< 900 \text{ N/mm}^2$ | 0.08 mm |
| Arbor size | 12 mm |
| Free length | 16 mm |
| Number of cutting edges Z | 4 |
| Series | TopCut |
| Grade | HB730 |
| Tool material | Solid carbide |
| Standard | Manufacturer's standard |
| Type | N |
| Helix angle | 30 degrees |
| Direction of infeed | horizontal and oblique |

| | |
|---|---------------------------|
| Cutting width a_e for milling operation | 0.05×D for copy milling |
| Machining strategy | HPC |
| Through-coolant | no |
| suitable arbor | GARANT TopCut |
| Type of product | Cutter insert for milling |

User data

| | Suitability | V_c | ISO code |
|--------------------------------|---|-----------|----------|
| Steel < 500 N/mm ² | suitable | 210 m/min | P |
| Steel < 750 N/mm ² | suitable | 170 m/min | P |
| Steel < 900 N/mm ² | suitable | 150 m/min | P |
| Steel < 1100 N/mm ² | suitable | 130 m/min | P |
| Steel < 1400 N/mm ² | suitable only under restricted conditions | 110 m/min | P |
| Steel < 55 HRC | suitable only under restricted conditions | 50 m/min | H |
| Steel < 60 HRC | suitable only under restricted conditions | 40 m/min | H |
| INOX < 900 N/mm ² | suitable | 80 m/min | M |
| INOX > 900 N/mm ² | suitable only under restricted conditions | 50 m/min | M |
| Ti > 850 N/mm ² | suitable only under restricted conditions | 80 m/min | S |
| GG(G) | suitable | 160 m/min | K |
| Oil | suitable only under restricted conditions | | |
| wet maximum | suitable | | |
| wet minimum | suitable only under restricted conditions | | |
| dry | suitable only under restricted conditions | | |

| | |
|-----|----------|
| Air | suitable |
|-----|----------|

Accessories

| | |
|---|-------------|
| Plug-in adapter for torque wrench Type 10X4 | 219986 10X4 |
|---|-------------|

| | |
|---------------------------|-------------|
| Assembly wrench Type 10X4 | 219987 10X4 |
|---------------------------|-------------|