



Protractor with adjustable beam, Graduated arc Ø×Stock length: 100X150mm



Order data

Order number	453401 100X150
GTIN	4067263062110
Item class	42F

Description

Version:

With longitudinally adjustable beam; beam end tapered 45°.

Open semicircular graduated arc with graduation 10 – 170°; reading 1°.

Scale matt chrome-plated. With clamping nut.

Technical description

Graduated arc Ø	100 mm
Error limit	±30 arc min.
Stock length	150 mm
Scale divisions	1 degrees
Standard	Works standard
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Packaging	Wallet
Calibration	F3

Type of product

Protractor

Services

CalibrationProtractor Type GRAD

025810 GRAD