

Garant**Turning insert, roughing CNMG, HB7020, Size / quantity: 160608/50**

Order data

Order number	GG2531 160608/50
GTIN	4067263092643
Item class	GGN

Technical description

Cutting depth a_p	0.55 - 5.5 mm
Cutting speed v_c main application	100 - 260 mm/min
Feed f	0.3 - 0.5 mm/rev.
Quantity	50
Contents	250334 HB7020
ISO code indexable insert	CNMG160608
Grade	HB7020
Chip breaker	SG
Type of product	Indexable insert for turning

Accessories

CNMG 160608 Grade HB7020

250334 HB7020