

Yale

Hydraulic hose HHC with factory fitting / filling, Length: 6m



Order data

Order number	086081 6
GTIN	2050000970351
Item class	08Y

Description

Version:

With hydraulic coupling No. 086085 size M1 (cylinder end) and screw-in connectors 3/8-NPT (pump end). External Ø 14 mm; internal Ø 6.3 mm (nominal bore); bursting pressure 2800 bar; minimum bending radius R = 100 mm.

Delivered only with a complete hydraulic system (pump, cylinder, hose) ex works with factory fitting, filling, and air bleeding.

All components and attachments satisfy **metric standard ranges**, which considerably simplifies assembly, service, and the procurement of spare parts. **100 % compatibility** with all commercially-available 700 bar hydraulic systems.

Note:

Closed systems are pre-mounted ex works, filled and air bled.

Technical description

Length	6 m
Type of product	Hydraulic accessories