

Garant**Turning insert, medium machining SCMT, HB7020, Size / quantity: 09T304/50****Order data**

Order number	GG2628 09T304/50
GTIN	4067263095583
Item class	GGN

Technical description

Quantity	50
Cutting speed v_c main application	130 - 280 mm/min
Contents	260762 HB7020
Cutting depth a_p	0.25 - 3.25 mm
Feed f	0.1 - 0.25 mm/rev.
ISO code indexable insert	SCMT09T304
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

SC.T 09T304 Grade HB7020

260762 HB7020