

**Turning insert, medium machining SCMT, HBT130, Size / quantity: 09T304/50****Order data**

Order number	GG2655 09T304/50
GTIN	4067263096801
Item class	GGN

Technical description

Cutting speed v_c main application	80 - 135 mm/min
Feed f	0.2 - 0.3 mm/rev.
Contents	260791 HBT130
Cutting depth a_p	0.25 - 3.25 mm
Quantity	50
ISO code indexable insert	SCMT09T304
Grade	HBT130
Chip breaker	MM
Type of product	Indexable insert for turning

Accessories

SCMT 09T304 Grade HBT130

260791 HBT130