

**Garant****Turning insert, medium machining SCGT, HU7310, Size / quantity: 120404/50****Order data**

Order number	GG2676 120404/50
GTIN	4067263098201
Item class	GGN

**Technical description**

Cutting depth $a_p$	0.25 - 4.25 mm
Feed $f$	0.1 - 0.3 mm/rev.
Cutting speed $v_c$ main application	350 - 600 mm/min
Contents	260765 HU7310
Quantity	50
ISO code indexable insert	SCGT120404
Grade	HU7310
Chip breaker	AM
Type of product	Indexable insert for turning

**Accessories**

SC.T 120404 Grade HU7310

260765 HU7310