

Garant**Turning insert, medium machining VCGT, HU7310, Size / quantity: 160402/50****Order data**

Order number	GG2686 160402/50
GTIN	4067263098621
Item class	GGN

Technical description

Feed f	0.1 - 0.3 mm/rev.
Cutting speed v_c main application	350 - 600 mm/min
Quantity	50
Cutting depth a_p	0.15 - 2.5 mm
Contents	261457 HU7310
ISO code indexable insert	VCGT160402
Grade	HU7310
Chip breaker	AM
Type of product	Indexable insert for turning

Accessories

VCGT 160402 Grade HU7310

261457 HU7310