



Digital caliper, measurement range: 150 mm ABS, Number of digital calipers: 3



Order data

Order number	412822 3
GTIN	4067263100003
Item class	42A

Description

Version:

Large, sharp-contrast digital display. The measuring faces are precision-lapped. Digital caliper with **absolute scale**, no zeroing required. Electronics switch off automatically after approx. 5 minutes and switch on again as soon as the tool is moved.

- **Very high accuracy due to the glass scale.**
- **The electronics are decoupled from the casing and incorporated directly in the sliding part. The gauging force is transmitted directly to the measurement jaws. This reduces the liability of the caliper to errors and increases the working life.**
- **With sturdy metal body.**

Supplied with:

3 × digital caliper No. 412821 size 150. Supplied with battery No. 081560 size CR2032.

Technical description

Power supply	Battery-powered
Calibration	A1
Standard	ISO 13385
Jaw length	40 mm
Depth gauge	rectangular 3.7×1.3

Auto switch-off	yes
Depth gauge available	yes
Measuring range	0 - 150 mm
Number of batteries contained	3
Scale divisions	0.01 mm
Scale divisions	0.0005 in
Measurement deviation E MPE	± 0.03 mm
Measured value saving	Once-off setting of the zero position
Article no of the battery / rechargeable battery fitted	081560 CR2032
Reversible reading	mm / inch
Material of the housing	Metal
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 3X200 mm	021000 3X200
DAkkS calibrationCalipers / depth gauges maximum measuring range 3X200 mm	021010 3X200

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Screw for depth gauge holder	412230