

**Garant**

**Vernier caliper set, measurement range: 150 mm, Number of digital calipers: 10**



## Order data

Order number	410102 10
GTIN	4067263100058
Item class	40Z

## Description

### Version:

Satin chromium plated anti-glare scales.

Fine, high-contrast scale.

Locking screw at the top.

Ergonomically optimised caliper. Error-free reading from colour-contrast scale.

Precision lapped measuring faces. Better reading due to a colour-contrast scale.

### Supplied with:

**10 × vernier calipers** No. 410100 size 150.

### Optional extras:

Thread table No. 412180 for caliper back.

## Technical description

Graduation	1/20 mm
Depth gauge available	yes
Jaw length	40 mm
Graduation	1/128 in

Depth gauge	rectangular 3.7×1.3
Calibration	A1
Reversible reading	mm / inch
Measurement deviation E MPE	± 0.05 mm
Standard	ISO 13385
Measuring range	0 - 150 mm
Scale divisions	0.05 mm
Packaging	Wallet
Locking	Locking screw at top
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Thread table	Calipers table
Type of product	Universal calipers

## Services

Calibration Calipers / depth gauges maximum measuring range 10X200 mm	021000 10X200
DAkkS calibration Calipers / depth gauges maximum measuring range 10X200 mm	021010 10X200

## Accessories

Table for calipers	412180
Synthetic leather case for vernier calipers	412500