

Garant**Vernier caliper set, measurement range: 150 mm Vernier 1/50, Number of digital calipers: 3**

Order data

Order number	410107 3
GTIN	4067263100027
Item class	40Z

Description

Version:

Satin chromium plated anti-glare scales.

Fine, high-contrast scale.

Locking screw at the top.

Ergonomically optimised caliper. Error-free reading from colour-contrast scale.

Precision lapped measuring faces.

Supplied with:

3 x vernier calipers No. 410105 size 150.

Optional extras:

Thread table No. 412180 for caliper back.

Technical description

Scale divisions	0.02 mm
Graduation	1/128 in
Measuring range	0 - 150 mm
Jaw length	40 mm
Packaging	Wallet

Standard	ISO 13385
Graduation	1/50 mm
Depth gauge	Ø 1.6
Depth gauge available	yes
Calibration	A1
Measurement deviation E MPE	±0.03 mm
Reversible reading	mm / inch
Locking	Locking screw at top
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Thread table	Calipers table
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 3X200 mm	021000 3X200
DAkkS calibrationCalipers / depth gauges maximum measuring range 3X200 mm	021010 3X200

Accessories

Synthetic leather case for vernier calipers	412500
---	--------