

Garant**Vernier caliper set, measurement range: 150 mm, Number of digital calipers: 3**

Order data

Order number	410102 3
GTIN	4067263100041
Item class	40Z

Description

Version:

Satin chromium plated anti-glare scales.

Fine, high-contrast scale.

Locking screw at the top.

Ergonomically optimised caliper. Error-free reading from colour-contrast scale.

Precision lapped measuring faces. Better reading due to a colour-contrast scale.

Supplied with:

3 × vernier calipers No. 410100 size 150.

Optional extras:

Thread table No. 412180 for caliper back.

Technical description

Measuring range	0 - 150 mm
Packaging	Wallet
Depth gauge available	yes
Graduation	1/128 in
Reversible reading	mm / inch

Measurement deviation E MPE	± 0.05 mm
Graduation	1/20 mm
Depth gauge	rectangular 3.7×1.3
Calibration	A1
Jaw length	40 mm
Standard	ISO 13385
Scale divisions	0.05 mm
Locking	Locking screw at top
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Thread table	Calipers table
Type of product	Universal calipers

Services

Calibration Calipers / depth gauges maximum measuring range 3X200 mm	021000 3X200
DAkkS calibration Calipers / depth gauges maximum measuring range 3X200 mm	021010 3X200

Accessories

Table for calipers	412180
Synthetic leather case for vernier calipers	412500