


Garant
Parallel arbor vibration damped, Plain shank, for cutter head Ø D: 12mm

Order data

Order number	210551 12
GTIN	4045197658876
Item class	21Z

Description
Version:

Precision-ground arbor for GARANT TopCut screw-in heads.

System radial run-out $\leq 10 \mu\text{m}$ due to the combination of taper and flat face.

With solid carbide core, without clamping flat.

Note:

Maximum milled depth = $L_1 + l$; l = see dimensions of the screw-in heads: No. 210050 – 210410.

Assembly wrench = No. 219987.

Plug-in adapter for torque wrench = No. 219986.

For long tool overhang, reduce technology data.

Technical description

for cutter head Ø D	12 mm
Shank Ø D ₅ h6	12 mm
Reach L ₁	25 mm
External Ø d ₁	11.8 mm
recommended tightening torque	10 Nm
Overall length L	70 mm
Series	TopCut
Adapter	Plain shank
Through-coolant	yes
Type of product	Threaded copy mill arbor

