

Garant

**Digital caliper set, with rectangular depth rod, measurement range: 150 mm
IP54 with data output, Number of digital calipers: 10**



Order data

Order number	412681 10
GTIN	4067263100225
Item class	41A

Description

Version:

Digital calipers to IP54 with data output. **Easy-to-read, high-contrast LCD display with 11.5 mm character height.** Very long battery running time due to modern energy-efficient measurement system. The system switches automatically into power-saving mode after 20 minutes; moving the caliper reactivates it. There is no loss of the measurement value or zero point. With preset (dimension selection in advance). **Ergonomic housing with easy-grip Haptoprene component.** The measuring faces are precision-lapped.

Advantage:

- **Ergonomic housing with easy-grip Haptoprene component.**
- **Long battery life.**
- **Large high-contrast LCD display with 11.5 mm character height.**
- **New modern design.**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Supplied with battery No. 081560 size CR2032. **10 x digital caliper**No. 412680 size 150.

Optional extras:

Data cable No. 498948, keyboard interface No. 498963

Spare part:

Data output cap No. 412237 size D, battery holder No. 412237 size B.

Technical description

Calibration	A1
Depth gauge	rectangular 3.7×1.3
Article no of the battery / rechargeable battery fitted	081560 CR2032
Measurement deviation E MPE	± 0.02 mm
Scale divisions	0.0005 in
Power supply	Battery-powered
Measuring range	0 - 150 mm
Scale divisions	0.01 mm
Number of batteries contained	10
Standard	ISO 13385
Reversible reading	mm / inch
IP Index of Protection	IP 54
Jaw length	40 mm
Interface	RS232C interface
Interface	USB interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 10X200 mm	021000 10X200
DAkkS calibrationCalipers / depth gauges maximum measuring range 10X200 mm	021010 10X200

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Screw for depth gauge holder	412236
Cover for digital calipers Type B	412237 B
Cover for digital calipers Type D	412237 D
Connection cable Type R2	498948 R2
Connection cable Type USB2	498948 USB2
Keyboard interfaceUSB Type G2	498963 G2