

**Garant**

**Digital caliper set, with rectangular depth rod, measurement range: 150 mm IP54 with data output, Number of digital calipers: 3**


**Order data**

Order number	412681 3
GTIN	4067263100201
Item class	41A

**Description**
**Version:**

Digital calipers to IP54 with data output. **Easy-to-read, high-contrast LCD display with 11.5 mm character height.** Very long battery running time due to modern energy-efficient measurement system. The system switches automatically into power-saving mode after 20 minutes; moving the caliper reactivates it. There is no loss of the measurement value or zero point. With preset (dimension selection in advance). **Ergonomic housing with easy-grip Haptoprene component.** The measuring faces are precision-lapped.

**Advantage:**

- **Ergonomic housing with easy-grip Haptoprene component.**
- **Long battery life.**
- **Large high-contrast LCD display with 11.5 mm character height.**
- **New modern design.**

**Function:**

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

**Supplied with:**

Supplied with battery No. 081560 size CR2032. **3 x digital caliper**No. 412680 size 150.

**Optional extras:**

Data cable No. 498948, keyboard interface No. 498963

**Spare part:**

Data output cap No. 412237 size D, battery holder No. 412237 size B.

## Technical description

Reversible reading	mm / inch
Number of batteries contained	3
Power supply	Battery-powered
Measurement deviation E MPE	$\pm 0.02$ mm
IP Index of Protection	IP 54
Depth gauge	rectangular 3.7×1.3
Scale divisions	0.01 mm
Scale divisions	0.0005 in
Article no of the battery / rechargeable battery fitted	081560 CR2032
Standard	ISO 13385
Calibration	A1
Measuring range	0 - 150 mm
Jaw length	40 mm
Interface	RS232C interface
Interface	USB interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

## Services

CalibrationCalipers / depth gauges maximum measuring range 3X200 mm	021000 3X200
DAkkS calibrationCalipers / depth gauges maximum measuring range 3X200 mm	021010 3X200

## Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Screw for depth gauge holder	412236
Cover for digital calipers Type B	412237 B
Cover for digital calipers Type D	412237 D
Connection cable Type R2	498948 R2
Connection cable Type USB2	498948 USB2
Keyboard interfaceUSB Type G2	498963 G2