

**Garant**
**APMT 180508 ER, HB7730, Type: GG**


## Order data

Order number	215256 GG
GTIN	4045197601056
Item class	21A

## Description

**Note:**

Standard application values for  $a_e = 0.3 \times D$  /  $a_p = 5$  mm,  $a_{p\max} = 9$  mm.

Corner radius: 0.8 mm

Feed  $f_z$  per tooth: 0.2 mm

## Technical description

Feed $f_z$ per tooth	0.2 mm
Type	GG
Corner radius	0.8 mm
ISO code indexable insert	APMT 180508 ER
Grade	HB7730
Tool material	Carbide
Type of product	Indexable insert for milling

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
GG(G)	suitable	250 m/min	K
wet maximum	suitable only under restricted conditions		
dry	suitable		