

**Garant**
**Parallel arbor, Plain shank, for cutter head Ø D: 16mm**

**Order data**

Order number	210550 16
GTIN	4045197522603
Item class	21Z

**Description**
**Version:**

Precision-ground arbor for GARANT TopCut screw-in heads.

**System radial run-out  $\leq 10 \mu\text{m}$**  due to the combination of taper and flat face.

With plain shank (for HSC machining). **Tolerance = h6.**

**Note:**

**Maximum milling depth** =  $L_1 + l$ ;  $l$  = see dimensions of the screw-in heads: No. 210050 – 210410.

Clamping wrench = No. 219987.

Insert for torque wrench = No. 219986.

For long tool overhang, reduce technology data.

**Technical description**

for cutter head Ø D	16 mm
Shank Ø D <sub>s</sub> h6	20 mm
External Ø d <sub>1</sub>	15.8 mm
recommended tightening torque	15 Nm
Overall length L	70 mm
Series	TopCut
Adapter	Plain shank
Through-coolant	yes
Type of product	Threaded copy mill arbor

