

Garant GRIDLINE

Tool cabinet complete with drawers 75 kg, 26×20G, Height mm / number of drawers: 800/6B



Order data

Order number	930605 800/6B
GTIN	4067263100645
Item class	9GK

Description

Version:

Completely equipped tool cabinet in 30×24G, with drawers 26×20G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Technical description

Usable height	700 mm
Usable height for drawers	700 mm
Drawer usable width in G	26

Drawer usable area in G	26×20
Drawer usable depth	500 mm
Number of doors	0
Drawer usable depth in G	20
Base cabinet underneath height-adjustable workstation	no
Depth	600 mm
Electronic locking system can be retrofitted	yes
Drawer usable width	650 mm
Number of drawers	6
Height	800 mm
Number of pull-out shelves	0
Width	750 mm
Weight	105 kg
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26×20G
Type of product	Tool cabinet