

Garant GRIDLINE

Tool cabinet complete with drawers 75 kg, 36×20G, Height mm / number of drawers: 800/7A**Order data**

Order number	930705 800/7A
GTIN	4067263100676
Item class	9GK

Description**Version:**

Completely equipped tool cabinet in 40×24G, with drawers 36×20G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Technical description

Usable height for drawers	700 mm
Number of drawers	7
Number of doors	0
Drawer usable depth in G	20

Drawer usable width	900 mm
Drawer usable width in G	36
Number of pull-out shelves	0
Drawer usable depth	500 mm
Drawer usable area in G	36×20
Base cabinet underneath height-adjustable workstation	no
Width	1000 mm
Electronic locking system can be retrofitted	yes
Depth	600 mm
Height	800 mm
Usable height	700 mm
Weight	149 kg
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	36×20G
Type of product	Tool cabinet