

Garant GRIDLINE

## Tool cabinet complete with drawers 200 kg, 36×20G, Height mm / number of drawers: 900/7A



### Order data

Order number	930715 900/7A
GTIN	4067263100744
Item class	9GK

### Description

#### Version:

Completely equipped tool cabinet in 40×24G, with drawers 36×20G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Drawers **50 mm with 75 kg** load capacity. Drawers **from 75 mm with 200 kg** load capacity.

#### Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

#### Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

### Technical description

Width	1000 mm
Base cabinet underneath height-adjustable workstation	no
Drawer usable width	900 mm

Drawer usable area in G	36x20
Usable height	800 mm
Height	900 mm
Drawer usable width in G	36
Number of pull-out shelves	0
Drawer usable depth in G	20
Electronic locking system can be retrofitted	yes
Drawer usable depth	500 mm
Weight	144 kg
Number of drawers	7
Number of doors	0
Depth	600 mm
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	200 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	36x20G
Type of product	Tool cabinet