

Garant GRIDLINE

Tool cabinet complete with drawers 75 kg, 36×20G, Height mm / number of drawers: 1500/12**Order data**

Order number	930705 1500/12
GTIN	4067263100720
Item class	9GK

Description**Version:**

Completely equipped tool cabinet in 40×24G, with drawers 36×20G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Technical description

Height	1500 mm
Drawer usable depth	500 mm
Number of pull-out shelves	0

Drawer usable depth in G	20
Usable height for drawers	1400 mm
Electronic locking system can be retrofitted	yes
Drawer usable area in G	36×20
Depth	600 mm
Drawer usable width in G	36
Weight	246 kg
Number of drawers	12
Base cabinet underneath height-adjustable workstation	no
Number of doors	0
Usable height	1400 mm
Drawer usable width	900 mm
Width	1000 mm
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	36×20G
Type of product	Tool cabinet