

Garant GRIDLINE

Tool cabinet complete with drawers 75 kg, 26×24G, Height mm / number of drawers: 1000/9A**Order data**

Order number	931105 1000/9A
GTIN	4067263091691
Item class	9GK

Description**Version:**

Completely equipped tool cabinet in 30×28G, with drawers 26×24G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Technical description

Number of drawers	9
Drawer usable width in G	26
ComfortClose	no

Electronic locking system can be retrofitted	yes
Number of pull-out shelves	0
Usable height	900 mm
Drawer usable area in G	26×24
Height	1000 mm
Ribbed rubber inlay with anti-roll lip on 3 sides	no
Drawer usable depth in G	24
Drawer usable width	650 mm
Base cabinet underneath height-adjustable workstation	no
Drawer usable depth	600 mm
Number of doors	0
Width	750 mm
Usable height for drawers	900 mm
Weight	170 kg
Depth	700 mm
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26×24G
Type of product	Tool cabinet