

Garant GRIDLINE

**Tool cabinet complete with drawers 200 kg, 26×24G, Height mm / number of drawers: 1000/8B****Order data**

|              |                |
|--------------|----------------|
| Order number | 931115 1000/8B |
| GTIN         | 4067263100966  |
| Item class   | 9GK            |

**Description****Version:**

Completely equipped tool cabinet in 30×28G, with drawers 26×24G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Drawers **50 mm with 75 kg** load capacity. Drawers **from 75 mm with 200 kg** load capacity.

**Colour:**

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

**Technical description**

|                            |    |
|----------------------------|----|
| Number of pull-out shelves | 0  |
| Drawer usable width in G   | 26 |

|   |  |
|---|--|
| Drawer usable depth in G                              | 24   |
| Height  | 1000 mm  |
| Width   | 750 mm   |
| Drawer usable area in G                               | 26×24  |
| Base cabinet underneath height-adjustable workstation | no   |
| Drawer usable width                                   | 650 mm   |
| ComfortClose  | no   |
| Weight  | 159 kg   |
| Number of drawers                                     | 8  |
| Depth   | 700 mm   |
| Number of doors                                       | 0  |
| Drawer usable depth                                   | 600 mm   |
| Usable height   | 900 mm   |
| Usable height for drawers                             | 900 mm   |
| Ribbed rubber inlay with anti-roll lip on 3 sides     | no   |
| Electronic locking system can be retrofitted          | yes  |
| Material thickness                                    | 1.2 mm   |
| Drawer/pull-out shelf load capacity                   | 200 kg   |
| Drawer runner extension (partial/full extension)      | 100 %  |
| Drawer runner extension                               | Anti-tilt lock   |
| Height adjustment interval                            | 25 mm  |
| Cylinder lock   | modular lock barrel  |
| Colour selection                                      | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Product name attribute                                | 26×24G   |
| Type of product                                       | Tool cabinet   |