

Garant GRIDLINE

## Tool cabinet complete with drawers 75 kg, 26×24G, Height mm / number of drawers: 1500/11



### Order data

Order number	931105 1500/11
GTIN	4067263100911
Item class	9GK

### Description

#### Version:

Completely equipped tool cabinet in 30×28G, with drawers 26×24G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

#### Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

#### Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

### Technical description

Drawer usable area in G	26×24
Drawer usable width in G	26
Ribbed rubber inlay with anti-roll lip on 3 sides	no

Usable height for drawers	1400 mm
Width	750 mm
Drawer usable width	650 mm
Base cabinet underneath height-adjustable workstation	no
Number of doors	0
Depth	700 mm
Usable height	1400 mm
ComfortClose	no
Number of pull-out shelves	0
Number of drawers	11
Weight	213 kg
Electronic locking system can be retrofitted	yes
Height	1500 mm
Drawer usable depth in G	24
Drawer usable depth	600 mm
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26x24G
Type of product	Tool cabinet