

Garant GRIDLINE

## Tool cabinet complete with drawers 200 kg, 36×24G, Height mm / number of drawers: 800/7A



### Order data

Order number	931315 800/7A
GTIN	4067263101048
Item class	9GK

### Description

#### Version:

Completely equipped tool cabinet in 40×28G, with drawers 36×24G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Drawers **50 mm with 75 kg** load capacity. Drawers **from 75 mm with 200 kg** load capacity.

#### Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

#### Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

### Technical description

Drawer usable area in G	36×24
Drawer usable width in G	36
Number of pull-out shelves	0

Width	1000 mm
Usable height	700 mm
Drawer usable width	900 mm
Number of drawers	7
Base cabinet underneath height-adjustable workstation	no
Height	800 mm
Number of doors	0
Depth	700 mm
Drawer usable depth	600 mm
Weight	162 kg
Drawer usable depth in G	24
Usable height for drawers	700 mm
Electronic locking system can be retrofitted	yes
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	200 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	36x24G
Type of product	Tool cabinet