

Garant GRIDLINE

Roller cabinet with drawers 75 kg, 26×24G, Height mm / number of drawers: 685/4A**Order data**

Order number	931145 685/4A
GTIN	4067263101093
Item class	9GK

Description**Version:****Complete with drawers 26×24G.**

Roller cabinet in 30×28G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With raised edge on 4 sides, ribbed rubber mat and 2-component Haptoprene push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

100% full extension drawers with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport. Absolutely necessary for all roller cabinets.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Usable height for drawers	400 mm
Height	685 mm

Data sheet

with anti-roll lip	yes
Width	750 mm
Individual drawer release system	One-hand
Drawer runner extension (partial/full extension)	100 %
Number of pull-out shelves	0
Usable height	400 mm
Treadless tyres	yes
Number of fixed wheels without parking brake	2
Drawer usable width in G	26
Drawer usable width	650 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer usable area in G	26×24
Drawer body usable height	400 mm
Depth	700 mm
Drawer body height	500 mm
Casing open at the top	no
Drawer usable depth	600 mm
ComfortClose	no
Number of drawers	4
maximum load capacity	600 kg
Drawer usable depth in G	24
Wheel Ø	125 mm
Weight	102 kg
Number of doors	0
Electronic locking system can be retrofitted	yes
Number of castors with parking brake	2
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm

Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7016, 5012, 5005
Product name attribute	26x24G
Type of product	Assembly trolley

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/931145-685/4A>