

Garant GRIDLINE

Roller cabinet with drawers 75 kg, 26×24G, Height mm / number of drawers: 685/4A



Order data

Order number	931145 685/4A
GTIN	4067263101093
Item class	9GK

Description

Version:

Complete with drawers 26×24G.

Roller cabinet in 30×28G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With raised edge on 4 sides, ribbed rubber mat and 2-component Haptoprene push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport. Absolutely necessary for all roller cabinets.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Usable height for drawers	400 mm
Height	685 mm

with anti-roll lip	yes
Width	750 mm
Individual drawer release system	One-hand
Drawer runner extension (partial/full extension)	100 %
Number of pull-out shelves	0
Usable height	400 mm
Treadless tyres	yes
Number of fixed wheels without parking brake	2
Drawer usable width in G	26
Drawer usable width	650 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer usable area in G	26×24
Drawer body usable height	400 mm
Depth	700 mm
Drawer body height	500 mm
Casing open at the top	no
Drawer usable depth	600 mm
ComfortClose	no
Number of drawers	4
maximum load capacity	600 kg
Drawer usable depth in G	24
Wheel Ø	125 mm
Weight	102 kg
Number of doors	0
Electronic locking system can be retrofitted	yes
Number of castors with parking brake	2
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm

Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26x24G
Type of product	Assembly trolley