

Garant GRIDLINE

Roller cabinet with drawers 75 kg, 20×20G, Height mm / number of drawers: 685/4A



Order data

| | |
|--------------|---------------|
| Order number | 930515 685/4A |
| GTIN | 4067263101086 |
| Item class | 9GK |

Description

Version:

Complete with drawers 20×20G.

Roller cabinet in 24×24G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With raised edge on 4 sides, ribbed rubber mat and 2-component Haptoprene push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock.

100% full extension drawers with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport. Absolutely necessary for all roller cabinets.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

| | |
|-------------------------|-------|
| Drawer usable area in G | 20×20 |
| with anti-roll lip | yes |

Data sheet

| | |
|--|----------------|
| Number of doors | 0 |
| Drawer usable depth in G | 20 |
| Number of castors with parking brake | 2 |
| Usable height for drawers | 400 mm |
| Usable height | 400 mm |
| Weight | 76 kg |
| Treadless tyres | yes |
| Drawer body height | 500 mm |
| Number of pull-out shelves | 0 |
| Drawer/pull-out shelf load capacity | 75 kg |
| Casing open at the top | no |
| Drawer usable width | 500 mm |
| Depth | 600 mm |
| Drawer body usable height | 400 mm |
| Number of drawers | 4 |
| Individual drawer release system | One-hand |
| Wheel Ø | 125 mm |
| maximum load capacity | 600 kg |
| Drawer runner extension (partial/full extension) | 100 % |
| Drawer usable width in G | 20 |
| Width | 600 mm |
| Number of fixed wheels without parking brake | 2 |
| Electronic locking system can be retrofitted | yes |
| ComfortClose | no |
| Height | 685 mm |
| Drawer usable depth | 500 mm |
| Material thickness | 1.2 mm |
| Drawer runner extension | Anti-tilt lock |
| Height adjustment interval | 25 mm |

Data sheet

| | |
|------------------------|----------------------------------|
| Cylinder lock | modular barrel |
| Colour selection | RAL 9002, 7035, 7016, 5012, 5005 |
| Product name attribute | 20x20G |
| Type of product | Assembly trolley |