

Garant GRIDLINE

Roller cabinet with drawers 75 kg, 20×20G, Height mm / number of drawers: 685/4A



Order data

Order number	930515 685/4A
GTIN	4067263101086
Item class	9GK

Description

Version:

Complete with drawers 20×20G.

Roller cabinet in 24×24G with 2 each ball-bearing fixed wheels and castors, Ø 125 mm, with treadless polyurethane tyres, castors with parking brakes. With raised edge on 4 sides, ribbed rubber mat and 2-component Haptoprene push handles. An anti-tilt device prevents more than one drawer being opened at one time. The casing can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm).

With **individual drawer release system** prevents the opening of drawers during transport. Absolutely necessary for all roller cabinets.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Drawer usable area in G	20×20
with anti-roll lip	yes

Number of doors	0
Drawer usable depth in G	20
Number of castors with parking brake	2
Usable height for drawers	400 mm
Usable height	400 mm
Weight	76 kg
Treadless tyres	yes
Drawer body height	500 mm
Number of pull-out shelves	0
Drawer/pull-out shelf load capacity	75 kg
Casing open at the top	no
Drawer usable width	500 mm
Depth	600 mm
Drawer body usable height	400 mm
Number of drawers	4
Individual drawer release system	One-hand
Wheel Ø	125 mm
maximum load capacity	600 kg
Drawer runner extension (partial/full extension)	100 %
Drawer usable width in G	20
Width	600 mm
Number of fixed wheels without parking brake	2
Electronic locking system can be retrofitted	yes
ComfortClose	no
Height	685 mm
Drawer usable depth	500 mm
Material thickness	1.2 mm
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm

Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Assembly trolley