

Garant GRIDLINE

Tool cabinet complete with drawers 200 kg, 36×24G, Height mm / number of drawers: 1000/8A**Order data**

Order number	931315 1000/8A
GTIN	4067263101079
Item class	9GK

Description**Version:**

Completely equipped tool cabinet in 40×28G, with drawers 36×24G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Drawers **50 mm with 75 kg** load capacity. Drawers **from 75 mm with 200 kg** load capacity.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Technical description

Depth	700 mm
Usable height for drawers	900 mm

Drawer usable depth in G	24
Number of doors	0
Number of pull-out shelves	0
Weight	195 kg
Usable height	900 mm
Base cabinet underneath height-adjustable workstation	no
Drawer usable width in G	36
Width	1000 mm
Drawer usable width	900 mm
Height	1000 mm
Electronic locking system can be retrofitted	yes
Number of drawers	8
Drawer usable area in G	36×24
Drawer usable depth	600 mm
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	200 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	36×24G
Type of product	Tool cabinet