

Garant GRIDLINE

Tool cabinet complete with drawers 75 kg, 36×24G, Height mm / number of drawers: 1000/7A**Order data**

Order number	931305 1000/7A
GTIN	4067263101024
Item class	9GK

Description**Version:**

Completely equipped tool cabinet in 40×28G, with drawers 36×24G. Can be locked centrally with a cylinder lock. **100% full extension drawers** with differential runners. Drawers with slots at 25 mm intervals to take slotted dividers (from drawer front height 75 mm). An anti-tilt device prevents more than one drawer being opened at one time.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

When lifting and transporting the cabinet, make sure the drawers are well secured within the casing.

Technical description

Depth	700 mm
Drawer usable width in G	36
Width	1000 mm

Base cabinet underneath height-adjustable workstation	no
Usable height for drawers	900 mm
Number of pull-out shelves	0
Number of drawers	7
Drawer usable width	900 mm
Weight	181 kg
Usable height	900 mm
Drawer usable depth in G	24
Drawer usable depth	600 mm
Electronic locking system can be retrofitted	yes
Height	1000 mm
Number of doors	0
Drawer usable area in G	36×24
Material thickness	1.2 mm
Drawer/pull-out shelf load capacity	75 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	36×24G
Type of product	Tool cabinet